

TECHSPEC[®] 50.8mm Diameter Protected Silver Coated, λ/10 Mirror



Stock #39-222 3-5 DAYS

-

1

+

A\$313.60

ADD TO CART

Qty 1-5

A\$313.60

Qty 6+

A\$251.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.80 +0.00/-0.20

Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate:

Fused Silica (Corning 7980)

Back Surface:

Commercial Polish
Surface Quality: 20-10
Dimensional Tolerance (mm): +0.0/-0.10
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): <180
Thickness (mm): 9.53 ±0.20
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant