

TECHSPEC® 50mm Dia., 4mm Thick, NIR I Coated λ/4 N-BK7 Window



Stock **#83-477** 3-5 DAYS

- 1 + **A\$195.20**

ADD TO CART

Qty 1-5
A\$195.20
Qty 6+
A\$156.00
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
64.17

Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):

45.00
Diameter (mm): 50.00 +0.0/-0.25
Thickness (mm): 4.00 ±0.20
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.1 (-30 to +70°C) 8.3 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Fine Ground
Index of Refraction n_d: 1.516
Knoop Hardness (kg/mm²): 610
Parallelism (arcmin): <1
Poisson's Ratio: 0.206
Substrate: N-BK7
Surface Flatness (P-V): λ/4
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 600 - 1050
Young's Modulus (GPa): 82
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant