

TECHSPEC® 50mm Dia., 5mm Thick, UV-VIS Coated λ/10 Fused Silica Window



Stock **#48-069** 3-5 DAYS

- 1 + **A\$416.00**

ADD TO CART

Qty 1-5
A\$416.00
Qty 6+
A\$332.80
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
67.8

Bevel:
Protective as needed

Clear Aperture (%):
80

Clear Aperture CA (mm):

40.00
Diameter (mm): 50.00 +0.00/-0.20
Thickness (mm): 5.00 ±0.10
Coating: UV-VIS (250-700nm)
Coating Specification: R _{abs} ≤1.0% @ 350 - 450nm R _{avg} ≤1.5% @ 250 - 700nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm³): 2.20
Edges: Fine Ground
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcsec): <5
Poisson's Ratio: 0.16
Substrate: Fused Silica (Corning 7980)
Surface Quality: 20-10
Transmitted Wavefront, P-V: λ/10
Type: Protective Window
Wavelength Range (nm): 250 - 700
Young's Modulus (GPa): 73
Damage Threshold, Reference: ☐ 3 J/cm² @ 355nm, 10ns 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant