

[See all 31 Products in Family](#)

**TECHSPEC® 50mm Dia. x 150mm FL 785nm V-Coat, UV PCX Lens**



Stock #25-923 **4 In Stock**

⊖ 1 ⊕ A\$534<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	A\$534.40 each
Qty 6-25	A\$427.20 each
Qty 26-49	A\$401.60 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Plano-Convex Lens **Type:**

**Physical & Mechanical Properties**

50.00 +0.0/-0.025 **Diameter (mm):**

Protective as needed **Bevel:**

Center Thickness CT (mm):

7.00

Centering (arcmin):

<1

Clear Aperture CA (mm):

49

Edge Thickness ET (mm):

2.29

## Optical Properties

Effective Focal Length EFL (mm):

150.00 @ 587.6nm

Substrate:

[Fused Silica](#)

f/#:

3

Numerical Aperture NA:

0.17

Coating:

785nm V-Coat

Back Focal Length BFL (mm):

145.20

Coating Specification:

R<sub>abs</sub> <0.25% @ 785nm

Design Wavelength DWL (nm):

785

Focal Length Tolerance (%):

±1

Radius R<sub>1</sub> (mm):

68.77

Surface Quality:

40-20

Power (P-V) @ 632.8nm:

1.5λ

Irregularity (P-V) @ 632.8nm:

λ/4

## Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 235:

[Compliant](#)

## Product Details

- <0.25% Reflection at 785nm
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- [405nm](#), [532nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCXLenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.