

50mm Dia. KRS-5, IR Holographic Wire Grid Polarizer



50mm Dia. KRS-5, IR Holographic Wire Grid Polarizer, #62-775

Stock **#62-775** 3-5 DAYS

⊖ 1 ⊕ **A\$3,784.00**

ADD TO CART

Qty 1-5
A\$3,784.00
Qty 6+
A\$3,024.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
34.0

Diameter (mm):
50.00

Extinction Ratio: 150:1 @ 3µm, 300:1 @ 15µm
Substrate: ☐ Thallium Bromoiodide (KRS-5)
Operating Temperature (°C): -20 to 75
Polarization: Notches on polarizer ring are aligned with wires of wire grid
Thickness (mm): 2.00
Transmission (%): >60
Type: Linear Polarizer
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Construction: Wire Grid
Groove Parallelism to Edge (°): N/A
Mount Thickness (mm): 6.0
Note: Notches on polarizer ring are aligned with wires of wire grid (max reflection)
Ring Thickness (mm): ±0.1
Wavelength Range (nm): 2500 - 30000
Surface Flatness (P-V): N/A
Damage Threshold, By Design: ☐ 50 W/cm²
Mount: Black Anodized Aluminum
Groove Density (grooves/mm): 2700.00

Regulatory Compliance

RoHS: Compliant
Reach 219: Compliant
Certificate of Conformance: View