


TECHSPEC® 50mm Dia. x 150mm FL, NIR I Coated, Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#18-190** 3-5 DAYS

- 1 +

A\$472.00

ADD TO CART

Qty 1-5

A\$472.00

Qty 6+

A\$377.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 -0.025

Effective Focal Length EFL (mm):
150.00 @587.6nm

Back Focal Length BFL (mm): 145.20
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 3 Rings
Irregularity (P-V) @ 632.8nm: 0.5 Rings
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 7.00 ±0.10
Edge Thickness ET (mm): 2.29
Radius R₁ (mm): 68.77
Clear Aperture CA (mm): 49
f/#: 3
Numerical Aperture NA: 0.17
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 1050
Damage Threshold, Reference: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant