

[See all 13 Products in Family](#)

**TECHSPEC® 50mm Dia. x 3mm Thick, Barium Fluoride Window**



Stock **#87-702** **14 In Stock**

A\$1,128<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	A\$1,128.00 each
Qty 11-25	A\$1,016.00 each
Qty 26-49	A\$960.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Protective Window Type:

**Physical & Mechanical Properties**

45.00 Clear Aperture CA (mm):

50.00 +0.0/-0.1 Diameter (mm):

3.00 ±0.1	Thickness (mm):
<3	Parallelism (arcmin):
+0.0/-0.1	Dimensional Tolerance (mm):
Protective as needed	Bevel:
90.00	Clear Aperture (%):
Fine Ground	Edges:
0.34	Poisson's Ratio:
53	Young's Modulus (GPa):
82.00	Knoop Hardness (kg/mm <sup>2</sup> ):

## Optical Properties

Uncoated	Coating:
Barium Fluoride (BaF <sub>2</sub> )	Substrate: <input type="checkbox"/>
1.48	Index of Refraction (n <sub>d</sub> ):
60-40	Surface Quality:
81.78	Abbe Number (v <sub>d</sub> ):
200 - 12000	Wavelength Range (nm):
λ/2	Surface Flatness (P-V):

## Material Properties

4.89	Density (g/cm <sup>3</sup> ):
18.1	Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C):

## Environmental & Durability Factors

Maximum: 800	Operating Temperature (°C):
--------------	-----------------------------

## Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

## Product Details



- Excellent Transmission from 200nm - 12μm
- Resistant to High-Energy Radiation
- Provide High Transmission without AR Coatings

TECHSPEC® Barium Fluoride (BaF<sub>2</sub>) Windows can be used in a variety of applications, such as infrared spectroscopy, due to their wide broadband transmission that extends from the deep ultraviolet to the long-wave infrared. Barium fluoride's low index of refraction of 1.48 provides high transmission without the need for anti-reflection coatings. Barium fluoride windows can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the ultraviolet range. While barium fluoride windows are less resistant to water than calcium fluoride, BaF<sub>2</sub> windows are the most resistant optical fluoride to high-energy radiation, but feature lower UV transmittance. BaF<sub>2</sub> has a Knoop hardness of 82.

**Note:** These optical windows are very sensitive to thermal shock.

Barium fluoride is a fast scintillator and can be used to detect X-rays, gamma rays, or other high energy particles such as 511 keV gamma photons in Positron Emission Tomography (PET). BaF<sub>2</sub> can also be used to detect high-energy neutrons and separate them from simultaneously occurring gamma photons using pulse shape discrimination techniques.

## Technical Information



### Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

### Compatible Mounts