

[See all 18 Products in Family](#)

TECHSPEC® 50mm Dia. x 200mm EFL, UV-VIS Coated, Near UV Achromatic Lens



Stock #35-997 **13 In Stock**

⊖ 1 ⊕ A\$443²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$443.20 each
Qty 6-25	A\$353.60 each
Qty 26-49	A\$332.80 each
Need More?	Request Quote

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

50.00 +0.0/-0.025 **Diameter (mm):**

49.0	Clear Aperture CA (mm):
<1	Centering (arcmin):
14.50 ±0.20	Center Thickness CT (mm):
10.00 ±0.10	Center Thickness CT 1 (mm):
4.50 ±0.10	Center Thickness CT 2 (mm):
10.57	Edge Thickness ET (mm):
Protective as needed	Bevel:

Optical Properties

200.00	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
192.01	Back Focal Length BFL (mm):
405.00	Focal Length Specification Wavelength (nm):
105.89	Radius R₁ (mm):
-92.87	Radius R₂ (mm):
-334.00	Radius R₃ (mm):
N-FK5 / F2HT	Substrate:
40-20	Surface Quality:
4	f#:
0.13	Numerical Aperture NA:
UV-VIS (345-700nm)	Coating:
R _{avg} ≤1.5% @ 345 - 700nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
345 - 700	Wavelength Range (nm):

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).



Product Details

- Excellent Transmission in 345 – 700nm Range
- Ideal for use with NUV LEDs and Mercury Lamps

- Low-Cost, Cemented Design

TECHSPEC® Near-UV (NUV) Achromatic Lenses are specifically designed to minimize the spot size for polychromatic illumination in the 345 – 700nm region. The achromatic lenses are ideal for use in fluorescence applications, as well as for simple focusing of common UV light sources, such as Mercury Arc Lamps, UV LEDs, and Tripled Nd:YAG lasers. Featuring a simple cemented design, the lenses are an excellent alternative to air-spaced doublets and triplets for the UV. TECHSPEC® Near-UV (NUV) Achromatic Lenses feature >90% transmission at 360nm and provide >50% transmission at 334nm. The lenses feature either N-FK5 or F2HT substrate and a UV-MS coating.

Technical Information



Compatible Mounts