

[See all 413 Products in Family](#)

TECHSPEC[®] 5.0mm Dia. x 30.0mm FL, YAG-BBAR, Inked, Plano-Convex Lens



YAG-BBAR Coated Plano-Convex (PCX) Lenses



Stock **#88-795-INK** [CONTACT US](#)

☐ [Other Coating Options](#)

-

1

+

A\$105⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$105.60 each
Qty 10-24	A\$95.20 each
Qty 25-49	A\$84.80 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

Diameter (mm):

5.00 ±0.025	
	Centering (arcmin):
<1	
	Center Thickness CT (mm):
1.60 ±0.05	
	Edge Thickness ET (mm):
1.40	
	Clear Aperture CA (mm):
4.5	
	Bevel:
Protective as needed	

Optical Properties	
	Effective Focal Length EFL (mm):
30.00 @ 587.6nm	
	Back Focal Length BFL (mm):
28.95	
	Coating:
YAG-BBAR (500-1100nm)	
	Coating Specification:
R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm	
	Substrate: ☐
N-BK7	
	Surface Quality:
40-20	
	Power (P-V) @ 632.8nm:
1.5λ	
	Irregularity (P-V) @ 632.8nm:
λ/4	
	Focal Length Tolerance (%):
±1	
	Radius R ₁ (mm):
15.50	
	f##:
6	
	Numerical Aperture NA:
0.08	
	Wavelength Range (nm):
500 - 1100	
	Damage Threshold, By Design: ☐
5 J/cm² @ 532nm, 10ns	

Regulatory Compliance	
	Certificate of Conformance:
View	

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Optimized for R<0.25% @ Both 532nm and 1064nm
- AR Coated to Provide <1.0% Reflectance per Surface for 500 - 1100nm
- Designed for 0° Angle of Incidence
- Various PCX Coating Options: [Uncoated](#), [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), and [VIS-EXT](#)

TECHSPEC® YAG-BBAR Coated Plano-Convex (PCX) Lenses have a positive focal length, making them ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. TECHSPEC® YAG-BBAR Coated Plano-Convex (PCX) Lenses are available in a wide variety of diameters and focal lengths. Identical designs of these PCX lenses are also offered [uncoated](#) or with broadband anti-reflective (BBAR) coatings, which include [MgF₂](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#), and [VIS-EXT](#).

Technical Information



N-BK7																											
Uncoated N-BK7 Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>T (%)</th></tr></thead><tbody><tr><td>200</td><td>~70</td></tr><tr><td>300</td><td>~70</td></tr><tr><td>400</td><td>~92</td></tr><tr><td>600</td><td>~92</td></tr><tr><td>800</td><td>~92</td></tr><tr><td>1000</td><td>~92</td></tr><tr><td>1200</td><td>~92</td></tr><tr><td>1400</td><td>~92</td></tr><tr><td>1600</td><td>~92</td></tr><tr><td>1800</td><td>~92</td></tr><tr><td>2000</td><td>~92</td></tr><tr><td>2200</td><td>~88</td></tr></tbody></table>	Wavelength (nm)	T (%)	200	~70	300	~70	400	~92	600	~92	800	~92	1000	~92	1200	~92	1400	~92	1600	~92	1800	~92	2000	~92	2200	~88	Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra. Click Here to Download Data
Wavelength (nm)	T (%)																										
200	~70																										
300	~70																										
400	~92																										
600	~92																										
800	~92																										
1000	~92																										
1200	~92																										
1400	~92																										
1600	~92																										
1800	~92																										
2000	~92																										
2200	~88																										
N-BK7 with MgF₂ Coating Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>T (%)</th></tr></thead><tbody><tr><td>200</td><td>~70</td></tr><tr><td>300</td><td>~70</td></tr><tr><td>400</td><td>~98</td></tr><tr><td>600</td><td>~98</td></tr><tr><td>800</td><td>~98</td></tr><tr><td>1000</td><td>~98</td></tr><tr><td>1200</td><td>~98</td></tr><tr><td>1400</td><td>~98</td></tr><tr><td>1600</td><td>~98</td></tr><tr><td>1800</td><td>~98</td></tr><tr><td>2000</td><td>~98</td></tr><tr><td>2200</td><td>~90</td></tr></tbody></table>	Wavelength (nm)	T (%)	200	~70	300	~70	400	~98	600	~98	800	~98	1000	~98	1200	~98	1400	~98	1600	~98	1800	~98	2000	~98	2200	~90	Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
Wavelength (nm)	T (%)																										
200	~70																										
300	~70																										
400	~98																										
600	~98																										
800	~98																										
1000	~98																										
1200	~98																										
1400	~98																										
1600	~98																										
1800	~98																										
2000	~98																										
2200	~90																										
N-BK7 with VIS-EXT Coating Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>T (%)</th></tr></thead><tbody><tr><td>200</td><td>~70</td></tr><tr><td>300</td><td>~70</td></tr><tr><td>400</td><td>~98</td></tr><tr><td>600</td><td>~98</td></tr><tr><td>800</td><td>~98</td></tr><tr><td>1000</td><td>~98</td></tr><tr><td>1200</td><td>~78</td></tr></tbody></table>	Wavelength (nm)	T (%)	200	~70	300	~70	400	~98	600	~98	800	~98	1000	~98	1200	~78	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data										
Wavelength (nm)	T (%)																										
200	~70																										
300	~70																										
400	~98																										
600	~98																										
800	~98																										
1000	~98																										
1200	~78																										
N-BK7 with VIS-NIR Coating Typical Transmission <table border="1"><thead><tr><th>Wavelength (nm)</th><th>T (%)</th></tr></thead><tbody><tr><td>200</td><td>~70</td></tr><tr><td>300</td><td>~70</td></tr><tr><td>400</td><td>~98</td></tr><tr><td>600</td><td>~98</td></tr><tr><td>800</td><td>~98</td></tr><tr><td>1000</td><td>~98</td></tr><tr><td>1200</td><td>~98</td></tr><tr><td>1400</td><td>~98</td></tr><tr><td>1600</td><td>~76</td></tr></tbody></table>	Wavelength (nm)	T (%)	200	~70	300	~70	400	~98	600	~98	800	~98	1000	~98	1200	~98	1400	~98	1600	~76	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data						
Wavelength (nm)	T (%)																										
200	~70																										
300	~70																										
400	~98																										
600	~98																										
800	~98																										
1000	~98																										
1200	~98																										
1400	~98																										
1600	~76																										



Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{avg}} \leq 0.4\% \text{ @ } 425 - 675\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{abs}} \leq 0.25\% \text{ @ } 532\text{nm}$$
$$R_{\text{abs}} \leq 0.25\% \text{ @ } 1064\text{nm}$$
$$R_{\text{avg}} \leq 1.0\% \text{ @ } 500 - 1100\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{avg}} \leq 0.5\% \text{ @ } 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 1mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{abs}} \leq 1.5\% \text{ @ } 750 - 800\text{nm}$$
$$R_{\text{abs}} \leq 1.0\% \text{ @ } 800 - 1550\text{nm}$$
$$R_{\text{avg}} \leq 0.7\% \text{ @ } 750 - 1550\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Compatible Mounts