

TECHSPEC[®] 50mm Dia x 40mm FL, MgF₂ Coated, Molded Aspheric Condenser Lens



TECHSPEC Molded Aspheric Condenser Lenses

Stock #15-197 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$96.00

ADD TO CART

Qty 1-10

A\$96.00

Qty 11+

A\$84.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.3

Effective Focal Length EFL (mm):
40.00 @ 587.6nm

Numerical Aperture NA:
0.625

Back Focal Length BFL (mm): 25.92
Substrate: ☐ Liba2000+
Focal Length Tolerance (%): ±5
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/5 x0.63; E 0.4 Polished Side: 5/5 x0.25; E 0.4
Clear Aperture CA (mm): 44.78
Edge Thickness ET (mm): 3.21
Center Thickness CT (mm): 21.42 ±0.30
f#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 50.00
Radius R₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant