

50mm Dia. ZnSe, IR Holographic Wire Grid Polarizer



Stock **#62-773** [CONTACT US](#)

- 1 + **A\$3,248.00**

ADD TO CART

Qty 1-5
A\$3,248.00
Qty 6+
A\$2,596.80
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Clear Aperture CA (mm):
34.0

Diameter (mm):
50.00

Extinction Ratio: 150:1 @ 3µm, 300:1 @ 10µm
Substrate: Zinc Selenide (ZnSe)
Operating Temperature (°C): -20 to 75
Polarization: Notches on polarizer ring are aligned with wires of wire grid
Thickness (mm): 2.00
Transmission (%): >50
Type: Linear Polarizer
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Construction: Wire Grid
Groove Parallelism to Edge (°): N/A
Mount Thickness (mm): 6.0
Note: Notches on polarizer ring are aligned with wires of wire grid (max. reflection)
Ring Thickness (mm): ±0.1
Wavelength Range (nm): 2500 - 19000
Surface Flatness (P-V): λ/10 @ 10.6µm
Damage Threshold, By Design: 50 W/cm²
Mount: Black Anodized Aluminum
Groove Density (grooves/mm): 2700.00

Regulatory Compliance

RoHS: Compliant
Reach 219: Compliant
Certificate of Conformance: View