

TECHSPEC® 50mm, f/16.0 Ci Series Fixed Focal Length Lens



50mm Focal Length

Stock **#86-620** **3 In Stock**

⊖ 1 ⊕ **A\$297⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-24	A\$297.00 each
Qty 25+	A\$268.00 each
Need More?	Request Quote

Product Downloads

General

Ci Series **Product Family:**
Fixed Focal Length Lens **Type:**

Physical & Mechanical Properties

Fixed **Iris Option:**
Length (mm):

49.50

30.5 **Maximum Diameter (mm):**

30.5 **Outer Diameter (mm):**

63 **Weight (g):**

2.06 **Maximum Rear Protrusion (mm):**

26.50 **Diameter (mm):**

Optical Properties

Horizontal Field of View @ Max Sensor Format:
42.8mm - 10.0°

Field of View at Max Sensor Format:
Horizontal: 42.7mm - 10°
Vertical: 32mm - 7.5°
Diagonal: 53.5mm - 12.5°

Horizontal Field of View, 2/3" Sensor:
42.8mm - 10.0°

Horizontal Field of View, 1/1.8" Sensor:
35.0mm - 8.2°

Horizontal Field of View, 1/2" Sensor:
31.1mm - 7.3°

Horizontal Field of View, 1/2.5" Sensor:
28.2mm - 6.6°

Horizontal Field of View, 1/3" Sensor:
23.3mm - 5.5°

Horizontal Field of View, 1/4" Sensor:
17.5mm - 4.1°

11.00 **Maximum Image Circle (mm):**

0.0054 **Numerical Aperture NA, Object Side:**

6 (4) **Number of Elements (Groups):**

50.00 **Focal Length FL (mm):**

250 - ∞ **Working Distance (mm):**

f/16 **Aperture (f/#):**

425 - 675nm BBAR **Coating:**

425 - 675nm BBAR **Coating Specification:**

35.62 **Entrance Pupil Position (mm):**

39.89 **Object Space Principal Plane (mm):**

-36.26 **Image Space Principal Plane (mm):**

0.26 **Maximum Distortion (%):**

-40.93 **Exit Pupil Position (mm):**

VIS **Lens Wavelength Range:**

Sensor

2/3" **Maximum Sensor Format:**

2.74 **Pixel Size (µm):**

Threading & Mounting

M30.5 x 0.50 (Female) **Filter Thread:**

[#89-943 \(Required\)](#) **Filter Thread Adapter:**

M30.5 x 0.5 (Male) **Front Thread:**

C-Mount **Mount:**

Environmental & Durability Factors

Storage Temperature (°C):
-20 to +60

Type of Ruggedization:
Industrial (Fixed Aperture with Simplified Mechanics)

Regulatory Compliance

RoHS 2015:
Compliant

REACH 201:
Compliant

Certificate of Conformance:
[View](#)

Product Details

These compact lenses are designed specifically for volume integration into applications such as analytical medical devices, including benchtop-based blood analyzers. For customized $f\#$ versions to best suit your instrumentation application needs and to discuss volume requirements, please [contact us](#).


- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8 μ m Pixel Size Sensors
- Instrumentation (Ci) Versions of our C Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 3.5mm to 50mm Focal Length
- **Ruggedized (Cr) Designs** Also Available

TECHSPEC® Ci Series Fixed Focal Length Lenses are a streamlined version of our C Series Fixed Focal Length Lenses. They feature the same low lens-to-lens variation and broadband anti-reflection (BBAR) coating for maximum light transmission, while offering reduced weight and size. An adjustable, lockable focus allows for setting and locking the best focus position for instrumentation integration. TECHSPEC® Ci Series Fixed Focal Length Lenses are designed specifically for volume integration into applications such as factory inspection and automation to benchtop biomedical devices. The Ci Series offers a wide range of aperture options, ensuring maximum flexibility of resolution, throughput, and depth of field.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.


Technical Information




#86-620, 50mm, $f/16.0$ Ci Series Fixed Focal Length Lens, Distortion Plot




#86-620, 50mm, $f/16.0$ Ci Series Fixed Focal Length Lens, Relative Illumination Plot




#86-620, 50mm, f/16.0 Ci Series Fixed Focal Length Lens, Working Distance versus Field of View Plot



#86-620, 50mm, f/16.0 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f16



#86-620, 50mm, f/16.0 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f16



#86-620, 50mm, f/16.0 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 1000mm Working Distance, f16



#86-620, 50mm, f/16.0 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 1000mm Working Distance, f16

Focal Length	A	B	C	D
6mm	M34.0 x 0.5	47.8mm	34mm	1.17mm
12mm	M22.0 x 0.75	29.0mm	22mm	0.96mm
16mm	M22.0 x 0.75	40.8mm	22mm	1.09mm
25mm	M22.0 x 0.75	29.9mm	22mm	1.33mm
35mm	M25.5 x 0.5	41mm	22.5mm	3.82mm
50mm	M30.5 x 0.5	49.5mm	30.5mm	2.06mm



Compatible Cameras