

[See all 26 Products in Family](#)

TECHSPEC® 50mm Square 45°, Green Dichroic Filter



Stock #47-950 [CONTACT US](#)

- 1 + A\$248⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$248.00 each
Need More?	Request Quote

Product Downloads

General

Dichroic Filter **Type:**

Physical & Mechanical Properties

50.0 x 50.0 **Dimensions (mm):**

50.00 **Length (mm):**

4.00 ±0.20 **Thickness (mm):**

Width (mm):

50.00	
<1	Parallelism (arcmin):
±0.25	Dimensional Tolerance (mm):
90.00	Clear Aperture (%):
Optical Properties	
45.00	Angle of Incidence (°):
535.00	Center Wavelength CWL (nm):
65.00	Full Width-Half Max FWHM (nm):
N-BK7	Substrate: <input type="checkbox"/>
Traditional Coated	Coating:
Green	Color:
R _{abs} = 99.7% @ 535nm R _{avg} >95% from 520-555nm	Reflection (%):
520 - 550	Reflection Wavelength (nm):
60-40	Surface Quality:
90.00	Transmission (%):
600 - 800	Transmission Wavelength (nm):
±15	Wavelength Tolerance (nm):
0.54	Center Wavelength CWL (μm):
0.07	Full Width-Half Max FWHM (μm):
Surface 1: Multi-Layer Dichroic Surface 2: Single Layer MgF ₂	Coating Specification:
520 - 800	Wavelength Range (nm):
λ/4	Surface Flatness (P-V):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Reflects Stated Color While Transmitting Remaining Visible Spectrum
- Ideal for Color Separation Applications
- Precision N-BK7 Substrates

TECHSPEC® 45° Reflective Dichroic Color Filters are designed to be used at a 45° angle of incidence and will reflect the stated color while transmitting the remaining visible wavelengths. EO's Reflective Dichroics boast higher performance and a better-quality substrate than other readily available color processing filters. Each filter provides greater than 98% reflection over the specified color range and greater than 90% transmission of the remaining wavelengths. TECHSPEC 45° Reflective Dichroic Color Filters are traditionally coated and feature an N-BK7 substrate. These filters are available in circular and square sizes.

Compatible Mounts

;