

TECHSPEC[®] 50mm Square 45°, Yellow Dichroic Filter



Stock #66-252 20+ In Stock

-

1

+

A\$248^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$248.00 each
Need More?	Request Quote

Product Downloads

General

Type:
Dichroic Filter

Physical & Mechanical Properties

Dimensions (mm):
50.0 x 50.0

Length (mm):
50.00

Thickness (mm):
4.00 ±0.20

Width (mm):

50.00	
<1	Parallelism (arcmin):
±0.25	Dimensional Tolerance (mm):
90.00	Clear Aperture (%):
Optical Properties	
45.00	Angle of Incidence (°):
520.00	Cut-Off Wavelength (nm):
N-BK7	Substrate:
Traditional Coated	Coating:
Yellow	Color:
R _{abs} = 50% @ 520nm R _{avg} > 98% @ 550 - 725nm	Reflection (%):
550 - 725	Reflection Wavelength (nm):
60-40	Surface Quality:
90.00	Transmission (%):
400 - 495	Transmission Wavelength (nm):
±15	Wavelength Tolerance (nm):
Surface 1: Multi-Layer Dichroic Surface 2: Single Layer MgF ₂	Coating Specification:
400 - 725	Wavelength Range (nm):
λ/4	Surface Flatness (P-V):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Reflects Stated Color While Transmitting Remaining Visible Spectrum
 - Ideal for Color Separation Applications
 - Precision N-BK7 Substrates
- TECHSPEC® 45° Reflective Dichroic Color Filters are designed to be used at a 45° angle of incidence and will reflect the stated color while transmitting the remaining visible wavelengths. EO's Reflective Dichroics boast higher performance and a better-quality substrate than other readily available color processing filters. Each filter provides greater than 98% reflection over the specified color range and greater than 90% transmission of the remaining wavelengths. TECHSPEC 45° Reflective Dichroic Color Filters are traditionally coated and feature an N-BK7 substrate. These filters are available in circular and square sizes.

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts

