

[See all 6 Products in Family](#)

## 50mm LensConnect BH Series Fixed Focal Length Lens



Computar Motorized LensConnect Fixed Focal Length Lenses

Stock **#24-194** **1 In Stock**

[Similar Products](#)

⊖ 1 ⊕ **A\$2,182.<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1+	<b>A\$2,182.00</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Computar Motorized LensConnect **Series:**

DL5028UC-MPY **Model Number:**

Fixed Focal Length Lens **Type:**

Motorized **Special Type of Lens:**

### Physical & Mechanical Properties

Motorized	<b>Iris Option:</b>
58.00	<b>Length (mm):</b>
59.5	<b>Outer Diameter (mm):</b>
173	<b>Weight (g):</b>
59.5 x 58	<b>Dimensions (mm):</b>

## Optical Properties

13.2° x 9.7° (D 16.3°)	<b>Horizontal Field of View, 1.1" Sensor:</b>
14.00	<b>Maximum Image Circle (mm):</b>
50.00	<b>Focal Length FL (mm):</b>
200 - ∞	<b>Working Distance (mm):</b>
f/2.8 - f/16	<b>Aperture (f/#):</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

1/1.1"	<b>Maximum Sensor Format:</b>
12.00	<b>Resolution (Megapixels):</b>
3.45	<b>Pixel Size (µm):</b>

## Hardware & Interface Connectivity

USB2.0 TypeA	<b>Control Interface:</b>
300 ±20	<b>Length of Cable (mm):</b>

## Threading & Mounting

M30.5 x 0.50	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- Focus and Iris Controlled via Simple USB Interface
- 12 MegaPixels, 1/1.1", C-Mount
- Focal Lengths Ranging from 8mm – 50mm
- [Variable Focal Length Option](#) Available

Computer Motorized LensConnect Fixed Focal Length Lenses are designed for remote focus and iris adjustment with a plug-and-play Windows or Linux compatible software. An integrated USB2.0 TypeA connector enables control and provides power to these lenses which are available in focal lengths of 8mm, 12mm, 16mm, 25mm, 35mm, and 50mm. Computer Motorized LensConnect Fixed Focal Length Lenses deliver high resolution for 12MP sensors, and the stepper motors enable precise focus control and high repeatability. These lenses are ideal for machine vision, inspection, and space constrained applications where manual adjustments are not possible.