

[See all 14 Products in Family](#)

50mW 1064nm LC Turnkey Laser Fiber SMA



Low Cost Turnkey Laser & Power Supply (Included)



Stock **#19-487** **1 In Stock**

-

1

+

A\$5,436⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$5,436.00 each
Need More?	Request Quote

Product Downloads

General	
	Warm-Up Time (minutes):
<10	
	Type of Laser:
Diode	
	Laser Class - CDRH:
IIIb	
	Mean Time to Failure MTTF (hours):
10000	

Physical & Mechanical Properties	
142.5 x 60 x 50	Dimensions (mm):
27.4	Beam Height from Base Plate (mm):
Optical Properties	
1,064.00	Wavelength (nm):
±2	Wavelength Tolerance (nm):
Infrared	Color:
0.22	Fiber Numerical Aperture NA (1/e ²):
Electrical	
50	Output Power (mW):
<2% RMS over 4 hours	Power Stability (%):
1	Modulation Frequency (kHz):
Hardware & Interface Connectivity	
88 x 145 x 83	Power Supply:
90-264VAC	Power Requirement:
Fiber-Coupled	Output Type:
SMA	Connector:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 233:

Product Details

- Multiple Colors and Wavelengths Available
- Ideal for Microscopy Applications
- TE Cooled

Low Cost Turnkey Lasers offer excellent beam quality and output powers up to 50mW. These lasers feature compact designs for simplified integration and manually adjustable output power through the control box. Each laser features TE cooling and flexible interface allowing for digital or analog modulation, with multiple color and wavelength options available. Low Cost Turnkey Lasers are ideal for research, flow cytometry, and microscope illumination applications.

Note: Power supply included. Fiber-coupled lasers include 1m SMA905 coupled fiber.

Technical Information

