

[See all 3 Products in Family](#)

## 51mm Aperture, Acktar Blackened Laser Beam Trap

See More by [Acktar](#)



Acktar Blackened Laser Beam Trap



Stock #13-516 **20+ In Stock**

- 1 + A\$632<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-2	A\$632.00 each
Qty 3+	A\$595.04 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Laser Beam Trap

Type:

LBD-T-51

Model Number:

### Physical & Mechanical Properties

Black Anodized Aluminum	<b>Construction:</b>
51mm (Dia.)	<b>Aperture Size:</b>
110.00	<b>Length (mm):</b>
63.5	<b>Outer Diameter (mm):</b>

## Optical Properties

Vacuum Black & Metal Velvet	<b>Coating:</b>
100 - 10000	<b>Wavelength Range (nm):</b>

## Electrical

20	<b>Maximum Incident Power Density (W/cm<sup>2</sup>):</b>
50	<b>Maximum Power (W):</b>

## Threading & Mounting

77	<b>Mount Diameter (mm):</b>
M6 x 1.0	<b>Mounting Threads:</b>

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 247:</b>

## Product Details

- Coated for High Absorbance of Laser Light
- Tubular Beam Trap or Thin, Flat Beam Block Designs
- M6 Tapped Hole for Easy Post Mounting

Acktar Blackened Laser Beam Traps and Blocks feature proprietary coatings designed to absorb incident laser light from the ultraviolet (UV) to the long-wave infrared (LWIR) spectrums. These Acktar coatings can achieve a reflectivity factor of less than  $10^{-6}$  (beam trap designs) and have laser damage thresholds up to  $20 \text{ W/cm}^2$ . An M6 tapped hole on both the beam trap and beam block designs allows for easy mounting to optical posts for integration into optical systems. Acktar Blackened Laser Beam Traps and Blocks are available in multiple sizes to accommodate small or large laser beams, increasing overall lab safety by reducing the risk of laser damage. The Flat Beam Block design features back screws for a 92mm cooling fan attachment, allowing for multiple blocks to be coupled to cover large areas.