

TECHSPEC® 540nm CWL, 12.5mm Dia, 50nm Bandwidth, OD 6 Fluorescence Filter



Stock **#86-344** 3-5 DAYS

[Additional Bandwidths](#)

1

A\$398.40

ADD TO CART

Qty 1-5

A\$398.40

Qty 6+

A\$331.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.10

Angle of Incidence (°):
0 ±5

Bandwidth (nm):
50.00

OD 6 Blocking Wavelength Range (nm): 450 - 500
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): 8.69
Center Wavelength CWL (nm): 540.00
Full Width-Half Max FWHM (nm): 56.00
Substrate:  Fused Silica (Corning 7980)
Minimum Transmission (%): >93
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Transmission (%): >93
Type: Bandpass Filter
Blocking Wavelength Range (nm): 250 - 1100
Construction: Mounted in Black Anodized Ring
Transmitted Wavefront, RMS: λ/4 (prior to coating)
Compatible Fluorophore: FITC Emission
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Mount Thickness (mm): 3.5 ±0.1
Substrate Thickness (mm): 2.00 ±0.25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant