

LightPath 354260 | 543nm Alignment, 0.16 NA Fiber Collimator w/ FC/APC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #13-555 3-5 DAYS

- 1 + **A\$432.00**

ADD TO CART

Qty 1-5
A\$432.00
Qty 6+
A\$316.80
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
15.29 @ 780nm

Numerical Aperture NA:
0.16

Substrate: D-ZK3
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.38
f#: 3.12
Bevel: Protective bevel as needed
Connector: FC/APC
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 20.2
Lightpath Lens Code: 354260
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite
Lens Included: #37-098
Alignment Wavelength (nm): 543

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant