


[See all 8 Products in Family](#)

5.7mm² DUV Photodiode with Ceramic Housing



DUVPhotodiodes

Stock **#84-982** **1 In Stock**

⊖ 1 ⊕ A\$160⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	A\$160.80 each
Qty 5-9	A\$141.60 each
Qty 10-24	A\$125.60 each
Need More?	Request Quote

Product Downloads

General

0.2@0V, 1kΩ **Rise Time (μs):**

Physical & Mechanical Properties

2.4x2.4 **Size of Active Area (mm):**

5.7 **Active Area (mm²):**

Optical Properties

980.00 **Peak Response Wavelength (nm):**

Electrical

0.5 **Responsivity @ 980nm (AW):**

Shunt Resistance @ V=-10mV (GΩ):
Minimum: 0.3
Typical: 1

0.34 **Responsivity @ 633nm (AW):**

0.12 **Responsivity @ 200nm (AW):**

65.00 **Capacitance @ V_R=0V (pF):**

Noise Equivalent Power NEP (W/ Hz^{1/2}):
3.6 x 10⁻¹⁴ @ 0 V, 200nm

5.00 **Maximum Reverse Voltage (V):**

Hardware & Interface Connectivity

Ceramic **Connector:**

Environmental & Durability Factors

-20 to +60 **Operating Temperature (°C):**

-20 to +80 **Storage Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Excellent UV Sensitivity
- High Shunt Resistance
- Low Capacitance

DUV Photodiodes are ideal for a wide variety of applications, including UV spectrophotometry and analytical and medical instrumentation. DUV Photodiodes are designed for enhanced responsivity from 200 – 400nm, and with sensitivity extending down to 190nm. DUV Photodiodes feature quartz windows and either metal or ceramic housing. Models with suppressed NIR performance are also available.