

TECHSPEC® 5mm 780nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock #47-778 3-5 DAYS

⊖ 1 ⊕ **A\$372.80**

ADD TO CART

Qty 1-5

A\$372.80

Qty 6+

A\$291.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Beam Deviation (arcmin):
±3

Bevel:
Protective bevel as needed

Clear Aperture (%):
90.00

Coating Specification:

R_{abs} <0.25% @ 780nm

Construction:

Cube

Design Wavelength DWL (nm):

780

Dimensions (mm):

5.0 x 5.0 x 5.0 ±0.1

Extinction Ratio:

1000:1

P-Polarization Transmission (%):

>95

S-Polarization Reflection (%):

>99.5

Substrate:

[N-BK7](#)

Surface Quality:

40-20

Type:

Linear Polarizer

Power (fringes) @ 632.8nm:

1.25

Irregularity (fringes) @ 632.8nm:

0.25

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Reach 219:

[Compliant](#)

Certificate of Conformance:

[View](#)
