


TECHSPEC<sup>®</sup> 5mm Dia x 10mm FL VIS 0° Coated, UV Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock #89-423 3-5 DAYS

- 1 +

A\$212.00

ADD TO CART

Qty 1-5

A\$212.00

Qty 6+

A\$169.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):  
5.00 +0.0/-0.025

Effective Focal Length EFL (mm):  
10.00 @ 587.6nm

|                                                                                           |
|-------------------------------------------------------------------------------------------|
| <b>Back Focal Length BFL (mm):</b><br>8.63                                                |
| <b>Coating:</b><br>VIS 0° (425-675nm)                                                     |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤0.4% @ 425 - 675nm                     |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980) |
| <b>Surface Quality:</b><br>40-20                                                          |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                     |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                               |
| <b>Focal Length Tolerance (%):</b><br>±1                                                  |
| <b>Centering (arcmin):</b><br><3                                                          |
| <b>Center Thickness CT (mm):</b><br>2.00 ±0.05                                            |
| <b>Edge Thickness ET (mm):</b><br>1.26                                                    |
| <b>Radius R<sub>1</sub> (mm):</b><br>4.59                                                 |
| <b>Clear Aperture CA (mm):</b><br>4.5                                                     |
| <b>f/#:</b><br>2                                                                          |
| <b>Numerical Aperture NA:</b><br>0.25                                                     |
| <b>Type:</b><br>Plano-Convex Lens                                                         |
| <b>Bevel:</b><br>Protective bevel as needed                                               |
| <b>Wavelength Range (nm):</b><br>425 - 675                                                |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>5 J/cm² @ 532nm, 10ns     |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |