

[See all 31 Products in Family](#)

**TECHSPEC® 5mm Dia. x 15mm FL 785nm V-Coat, UV PCX Lens**



Stock #25-896 **5 In Stock**

⊖ 1 ⊕ **A\$227<sup>.20</sup>**

**ADD TO CART**

Volume Pricing

Qty 1-5	<b>A\$227.20</b> each
Qty 6-25	<b>A\$182.40</b> each
Qty 26-49	<b>A\$171.20</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Plano-Convex Lens **Type:**

**Physical & Mechanical Properties**

5.00 +0.0/-0.025 **Diameter (mm):**

Protective as needed **Bevel:**

Center Thickness CT (mm):  
1.70

Centering (arcmin):  
<1

Clear Aperture CA (mm):  
4.5

Edge Thickness ET (mm):  
1.23

## Optical Properties

Effective Focal Length EFL (mm):  
15.00 @ 587.6nm

Substrate:   
[Fused Silica](#)

f#:  
3

Numerical Aperture NA:  
0.17

Coating:  
785nm V-Coat

Back Focal Length BFL (mm):  
13.83

Coating Specification:  
R<sub>abs</sub> <0.25% @ 785nm

Design Wavelength DWL (nm):  
785

Focal Length Tolerance (%):  
±1

Radius R<sub>1</sub> (mm):  
6.88

Surface Quality:  
40-20

Power (P-V) @ 632.8nm:  
1.5λ

Irregularity (P-V) @ 632.8nm:  
λ/4

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 235:  
[Compliant](#)

## Product Details

- <0.25% Reflection at 785nm
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- [405nm](#), [532nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCXLenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.