

TECHSPEC® 5mm Dia. x 25mm FL, VIS-NIR Coated, Double-Convex Lens



Stock **#63-662** 3-5 DAYS

[Other Coating Options](#)



1



A\$83.20

ADD TO CART

Qty 1-9
A\$83.20
Qty 10+
A\$74.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Back Focal Length BFL (mm):
24.50

Effective Focal Length EFL (mm): 25.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.50
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 1.26
Radius R₁=R₂ (mm): 25.58
Clear Aperture CA (mm): 4.5
f/#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant