


TECHSPEC[®] 6" Dia, 24" FL 320-450nm, Spherical Mirror



Stock **#72-979** 1 In Stock

-

1

+

A\$2,096⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$2,096.00 each
Qty 6-24	A\$1,676.80 each
Need More?	Request Quote

Product Downloads

General

Spherical Mirror

Type:

Physical & Mechanical Properties

152.40 +1.5/-0

Diameter (mm):

Ground

Back Surface:

6.0	Diameter (inches):
+0.06/-0	Diameter Tolerance (inches):

1.00	Edge Thickness ET (inches):
25.40	Edge Thickness ET (mm):

+0.0/-15	Edge Thickness Tolerance (%):
----------	-------------------------------

Optical Properties

Dielectric	Coating Type:
Dielectric Mirror (320-450nm)	Coating:

320 - 450	Wavelength Range (nm):
609.60	Effective Focal Length EFL (mm):

BOROFLOAT®SUPREMAX®	Substrate: □
f/4	Aperture (f/#):

R _{avg} >98% @ 340 - 488nm (0°, All Polarizations) R _{avg} >98% @ 320 - 450nm (45°, All Polarizations) R _{avg} >99% @ 320 - 450nm (45°, S-Polarization)	Coating Specification:
24.00	Effective Focal Length EFL (inches):

±2	Focal Length Tolerance (%):
λ/4	Surface Accuracy:

60-40	Surface Quality:
0.5 J/cm² @ 355nm, 20ns, 20Hz	Damage Threshold, By Design: □

1,219.20	Radius of Curvature (mm):
----------	---------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Ideal for Multispectral Focusing Applications
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Multiple Sizes Available

TECHSPEC® Broadband Dielectric Spherical Mirrors are ideal for light collection in multispectral imaging applications. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. ABOROFLOAT® substrate provides a good combination of performance and value. TECHSPEC® Broadband Dielectric Spherical Mirrors are available in diameters ranging from 25.4 to 152.4mm for ease of system integration. These mirrors collect and focus light without introducing chromatic aberration.

Technical Information

