

TECHSPEC®

6" Diameter x 48" FL Protected Gold, Parabolic Mirror



Stock #32-072-566

3-5 DAYS

-

1

+

A\$1,369.60

ADD TO CART

Qty 1-4
A\$1,369.60
Qty 5+
A\$1,164.80
Volume Pricing
Request Quote

Get Product Downloads

Substrate:

BOROFLOAT®

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 6.0 +0.06/-0
Diameter (mm): 152.40 +1.5/-0
Effective Focal Length EFL (inches): 48.0
Effective Focal Length EFL (mm): 1,219.20
Radius of Curvature (mm): 2,438.40
Aperture (f/#): f/8
Coating: Protected Gold (700-10000nm)
Coating Specification: Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 138
Edge Thickness ET (inches): 1.00
Edge Thickness ET (mm): 25.40
Type: Parabolic Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant