

## 600 Grooves, 25mm Square, 1600nm NIR Ruled Grating



Stock **#54-851** 6 In Stock

-

1

+

A\$296<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | A\$296.00 each                |
| Qty 10-24      | A\$266.40 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                     |
|----------------------------------|---------------------|
| Reflective Diffraction Grating   | Type:               |
| Physical & Mechanical Properties |                     |
| 25.0 x 25.0 ±0.5                 | Dimensions (mm):    |
| 90                               | Clear Aperture (%): |
| Ruled Grating                    | Construction:       |

|                                   |  |
|-----------------------------------|--|
| Direction of Grooves:             |  |
| Parallel to Short Dimension       |  |
|                                   |  |
| Length (mm):                      |  |
| 25.00                             |  |
|                                   |  |
| Thickness (mm):                   |  |
| 9.50 ±0.5                         |  |
|                                   |  |
| Width (mm):                       |  |
| 25.00                             |  |
|                                   |  |
| Alignment of Grooves to Edge (°): |  |
| ±0.5                              |  |

|                                     |  |
|-------------------------------------|--|
| Optical Properties                  |  |
|                                     |  |
| Groove Density (grooves/mm):        |  |
| 600                                 |  |
|                                     |  |
| Wavelength Range (nm):              |  |
| 700 - 3000                          |  |
|                                     |  |
| Blaze Wavelength (nm):              |  |
| 1600                                |  |
|                                     |  |
| Blaze Angle (°):                    |  |
| 28.68                               |  |
|                                     |  |
| Coating:                            |  |
| Bare Gold                           |  |
|                                     |  |
| Substrate: <input type="checkbox"/> |  |
| Float Glass                         |  |

|                             |  |
|-----------------------------|--|
| Regulatory Compliance       |  |
|                             |  |
| RoHS 2015:                  |  |
| <a href="#">Compliant</a>   |  |
|                             |  |
| Certificate of Conformance: |  |
| <a href="#">View</a>        |  |
|                             |  |
| Reach 247:                  |  |
| <a href="#">Compliant</a>   |  |



## Product Details

- Increased Reflection from 700 - 1100nm

Near-IR (NIR) Reflective Gold Gratings are ruled gold-coated versions of our commercial gratings. These gratings provide increased reflection from 700 - 1100nm. This makes them an excellent choice for applications such as fiber optic pulse compression and spectroscopy setups using [silicon detectors](#). Near-IR (NIR) Reflective Gold Gratings feature a float glass substrate and a ruled grating construction. The gratings are available in three sizes, with varying groove densities and blaze wavelengths.

**Handling Gratings:** Gratings require special handling, making them prone to fingerprints and aerosols. Gratings should only be handled by the edges. Before attempting to clean a grating, please [contact us](#).

## Technical Information



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

---

;