

TECHSPEC[®] 600-1050nm, 25mm Square, Ultrafast-Enhanced Silver Coated, λ/10 Mirror



Stock #21-999 3-5 DAYS

-

1

+

A\$198.40

ADD TO CART

Qty 1-5

A\$198.40

Qty 6+

A\$158.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate:
[Fused Silica](#) (Corning 7980)

Back Surface:
Commercial Polish

Surface Quality:

20-10
Dimensions (mm): 25.0 x 25.0
Dimensional Tolerance (mm): +0.00/-0.20
Coating Specification: R _{avg} >99% @ 600 - 1000nm, 0° R _s >99% @ 540 - 1000nm, 45° R _p >98.5% @ ~730 - 870nm, 45°
Coating: Ultrafast-Enhanced Silver (600-1000nm)
Coating Type: Ultrafast-Enhanced Silver
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 4.00 ±0.20
Type: Flat Mirror
Wavelength Range (µm): 0.60 - 1.05
Wavelength Range (nm): 600 - 1050
Length (mm): 25.00
Width (mm): 25.00
GDD Specification: 0 ±20fs ² @ 600 - 1050nm
Damage Threshold, Reference: ☐ 0.3 J/cm ² , 100 Hz, 48fs FWHM, 800nm, S-Pol, 1 Pulse 0.16 J/cm ² , 100 Hz, 48fs FWHM, 800nm, S-Pol, 1000 Pulses

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View