


[See all 72 Products in Family](#)

**TECHSPEC® 600 x 1000mm Linear Polarizing Film (XP42-18) with Adhesive**



Stock **#29-491** **5 In Stock**

⊖ 1 ⊕ **A\$704<sup>.00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>A\$704.00</b> each
Qty 11-25	<b>A\$618.56</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Linear Polarizer **Type:**

Polarization axis is parallel to first listed dimension **Note:**

**Physical & Mechanical Properties**

600.0 x 1000.0 +5.0/0.0 **Dimensions (mm):**

0.22 ±0.03 **Thickness (mm):**

Polarizing Film

**Construction:**

**Optical Properties**

**Coating:**

Pressure Sensitive Adhesive (PSA) one-sided

**Extinction Ratio:**

9000:1 (nominal at 555nm)

**Substrate:** □

**Polymer Film XP42-18**

**Transmission (%):**

Single: 42 ±2  
Parallel: 36.4  
Crossed: <0.004 (nominal at 555nm)

**Wavelength Range (nm):**

400 - 700

**Polarization Efficiency (%):**

>99.98 (nominal at 555nm)

**Transmission, Single (%):**

42 ±2

**Transmission, Parallel (%):**

36.4

**Transmission, Crossed (%):**

<0.004 (nominal at 555nm)

**Regulatory Compliance**

**RoHS 2015:**

Compliant

**Certificate of Conformance:**

[View](#)

**Reach 247:**

Compliant

**Product Details**

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available



Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

**Note:** Polarizer Film with adhesive available.

**Immediate Custom Quotes Available**

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

**Technical Information**



XP44 - Linear Polarizer

