



TECHSPEC[®] 6.0mm Dia. x -9 FL, 1064nm V-Coat, UV Plano-Concave Lens



Stock #21-026 3-5 DAYS

-

1

+

A\$211.20

ADD TO CART

Qty 1-5

A\$211.20

Qty 6+

A\$168.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-9.00

Substrate: Fused Silica (Coming 7980)
f#: 1.5
Numerical Aperture NA: 0.33
Coating: 1064nm V-Coat
Type: Plano-Concave Lens
Back Focal Length BFL (mm): -10.38
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 5.4
Coating Specification: R_{abs} <0.25% @ 1064nm
Design Wavelength DWL (nm): 1064
Edge Thickness ET (mm): 3.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Note: Max. Flat Annulus is 0.3mm
Radius R₁ (mm): -4.13
Surface Quality: 40-20
Damage Threshold, By Design: 15 J/cm² @ 1064nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View