

TECHSPEC[®] 6.0mm Dia. x 9.0mm FL, VIS-NIR, Inked, Plano-Convex Lens



Stock **#45-466-INK** 10-15 DAYS
[Other Coating Options](#)

-

1

+

A\$80.80

ADD TO CART

Qty 1-9
A\$80.80
Qty 10+
A\$72.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00 ±0.025

Effective Focal Length EFL (mm):
9.00 @ 587.6nm

Back Focal Length BFL (mm): 7.95
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-SF5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.75 ±0.05
Edge Thickness ET (mm): 0.95
Radius R₁ (mm): 6.05
Clear Aperture CA (mm): 5.4
f#: 1.5
Numerical Aperture NA: 0.33
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View