

TECHSPEC[®] 6.0mm Diameter x 48.0mm FL, 532nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock **#69-369** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$71.20

ADD TO CART

Qty 1-9

A\$71.20

Qty 10+

A\$64.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Effective Focal Length EFL (mm):

48.00 @ 587.6nm
Back Focal Length BFL (mm): 46.95
Coating: Laser V-Coat (532nm)
Coating Specification: R _{abs} <0.25% @ 532nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 1.60 ±0.05
Edge Thickness ET (mm): 1.42
Radius R₁ (mm): 24.81
Clear Aperture CA (mm): 5.4
f/#: 8.00
Numerical Aperture NA: 0.06
Design Wavelength DWL (nm): 532
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant