

6.0X Coaxial Zoom Lens, 0.37X - 2.23X Range



6.0X Coaxial Zoom Lens, 0.37X - 2.23X Range, #83-895

Stock **#83-895** **1 In Stock**

⊖ 1 ⊕ A\$4,097⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$4,097.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

High Magnification Zoom Lens **Type:**
In-Line Illumination **Type of Illumination:**

Physical & Mechanical Properties

680.00

Weight (g):

Optical Properties

Horizontal Field of View, 1/2" Sensor:
17.3 - 2.9mm

Numerical Aperture NA:
0.04 - 0.043

Zoom Ratio:
6:1

Primary Magnification PMAG:
0.37X - 2.23X

Working Distance (mm):
195.00

Distortion (%):
0.79 @ Min FOV, 1/2" Sensor
0.26 @ Max FOV, 1/2" Sensor

Depth of Field (mm):
10.0 - 0.6

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
1/2"

Threading & Mounting

Mount:
C-Mbunt

Regulatory Compliance

Certificate of Conformance:
[View](#)

PRODUCT DETAILS

- Robust Housing with Incremental Zoom Control
- Coaxial In-Line Illumination Option with 1/4" Fiber Port
- High Resolution Optical Design

The EO Precision Zoom Lenses are ideal for inspecting small details, especially electronic components. All lenses feature a robust, anodized aluminum housing, as well as an incremental (or detented) zoom for easy integration. With a working distance of 195mm, the 0.37X–2.23X lens is ideal for applications requiring a large object standoff or field of view. The 0.7X–4.5X lens features a working distance of 92mm and is available in coaxial or standard models. In addition, all 0.7X–4.5X lens models feature an option for an inner focus to allow them to image a large depth of field without moving the whole lens or object under inspection.