

**TECHSPEC® 6.0mm Diameter x -9 FL, NIR II Inked, Plano-Concave Lens**



Stock **#67-983-INK** 10-15 DAYS  
[Other Coating Options](#)

- 1 + **A\$78.40**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| A\$78.40                      |
| Qty 10+                       |
| A\$70.40                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Diameter (mm):**  
6.00 ±0.025

**Effective Focal Length EFL (mm):**  
-9.00

|                                                                                                                                                         |
|---------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Substrate:</b> <div><div></div><div>N-SF11</div></div>                                                                                               |
| <b>f/#:</b><br>1.5                                                                                                                                      |
| <b>Coating:</b><br>NIR II (750-1550nm)                                                                                                                  |
| <b>Type:</b><br>Plano-Concave Lens                                                                                                                      |
| <b>Wavelength Range (nm):</b><br>750 - 1550                                                                                                             |
| <b>Back Focal Length BFL (mm):</b><br>-9.84                                                                                                             |
| <b>Center Thickness CT (mm):</b><br>1.50                                                                                                                |
| <b>Center Thickness Tolerance (mm):</b><br>±0.05                                                                                                        |
| <b>Centering (arcmin):</b><br><3                                                                                                                        |
| <b>Clear Aperture CA (mm):</b><br>5.40                                                                                                                  |
| <b>Coating Specification:</b><br>R <sub>abs</sub> ≤1.5% @ 750 - 800nm<br>R <sub>abs</sub> ≤1.0% @ 800 - 1550nm<br>R <sub>avg</sub> ≤0.7% @ 750 - 1550nm |
| <b>Edge Thickness ET (mm):</b><br>2.04                                                                                                                  |
| <b>Focal Length Specification Wavelength (nm):</b><br>587.6                                                                                             |
| <b>Focal Length Tolerance (%):</b><br>±1.00                                                                                                             |
| <b>Radius R<sub>1</sub> (mm):</b><br>-7.06                                                                                                              |
| <b>Surface Quality:</b><br>40-20                                                                                                                        |
| <b>Damage Threshold, By Design:</b> <div><div></div><div>8 J/cm<sup>2</sup> @ 1064nm, 10ns</div></div>                                                  |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                                                                                   |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                                                                             |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br>Compliant                                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |