

[See all 280 Products in Family](#)

TECHSPEC[®] 6.25mm Dia. x 12.5mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-304** 20+ In Stock

☐ [Other Coating Options](#)

-

1

+

A\$129^{.60}

ADD TO CART

Volume Pricing	
Qty 1-5	A\$129.60 each
Qty 6-25	A\$104.00 each
Qty 26-49	A\$96.80 each
Need More?	Request Quote

Product Downloads

General

Type:

Achromatic Lens

Physical & Mechanical Properties

Diameter (mm):

6.25 +0.0/-0.025

5.625	Clear Aperture CA (mm):
<1	Centering (arcmin):
3.80 ±0.10	Center Thickness CT (mm):
3.00 ±0.05	Center Thickness CT 1 (mm):
0.80 ±0.05	Center Thickness CT 2 (mm):
3.12	Edge Thickness ET (mm):
Protective as needed	Bevel:

Optical Properties	
12.50	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
10.36	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
8.63	Radius R ₁ (mm):
-5.29	Radius R ₂ (mm):
-51.17	Radius R ₃ (mm):
N-BAF10 / N-SF10	Substrate: □
40-20	Surface Quality:
2.00	f/#:
0.25	Numerical Aperture NA:
VIS-NIR (400-1000nm)	Coating:
R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
400 - 1000	Wavelength Range (nm):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Designed for 0° Angle of Incidence
 - Less Than 0.25% Reflectance Per Surface @880nm
 - **MgF₂** and **VIS 0°** Coated Achromats Also Available
- TECHSPEC® VIS-NIR Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations. TECHSPEC® VIS-NIR Coated Achromatic Lenses have visible/near-infrared broadband anti-reflection coating, which is specially optimized to yield maximum transmission (>99%) in the near-infrared. The achromatic lenses reduce reflection to less than 0.25 percent per surface at 880nm. **Magnesium Fluoride** coated and **VIS 0°** coated achromats are also available.

Technical Information



Coating Curves

Compatible Mounts