

TECHSPEC® 6.25mm Dia. x 12.5mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-304-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 + **A\$131.20**

ADD TO CART

Qty 1-5
A\$131.20
Qty 6+
A\$104.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.25 ±0.025

Effective Focal Length EFL (mm):
12.50

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 10.36
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 5.625
Centering (arcmin): <1
Center Thickness CT (mm): 3.80 ±0.10
Center Thickness CT 1 (mm): 3.00 ±0.05
Center Thickness CT 2 (mm): 0.80 ±0.05
Radius R₁ (mm): 8.63
Radius R₂ (mm): -5.29
Radius R₃ (mm): -51.17
Edge Thickness ET (mm): 3.12
Substrate: ☐ N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View