

TECHSPEC[®] 6.25mm Dia. x 7.5mm FL, VIS 0° Coated, Achromatic Lens



Stock **#49-936** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$107.20

ADD TO CART

Qty 1-5

A\$107.20

Qty 6+

A\$85.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):

6.25 +0.0/-0.025

Effective Focal Length EFL (mm):

7.50

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 4.45
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 5.625
Centering (arcmin): <3
Center Thickness CT (mm): 6.00 ±0.10
Center Thickness CT 1 (mm): 5.00 ±0.05
Center Thickness CT 2 (mm): 1.00 ±0.05
Radius R₁ (mm): 5.60
Radius R₂ (mm): -3.71
Radius R₃ (mm): -11.34
Edge Thickness ET (mm): 4.61
Substrate: ☐ N-BAF10 / N-SF57
Surface Quality: 40-20
f/#: 1.2
Numerical Aperture NA: 0.42
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View