

TECHSPEC® 6.25mm Dia. x 30mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-308-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

A\$131.20

ADD TO CART

Qty 1-5

A\$131.20

Qty 6+

A\$104.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.25 ±0.025

Effective Focal Length EFL (mm):
30.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 28.43
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 5.625
Centering (arcmin) : <1
Center Thickness CT (mm) : 3.20 ±0.10
Center Thickness CT 1 (mm) : 2.30 ±0.05
Center Thickness CT 2 (mm) : 0.90 ±0.05
Radius R₁ (mm) : 18.11
Radius R₂ (mm) : -13.51
Radius R₃ (mm) : -39.29
Edge Thickness ET (mm) : 2.80
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 4.8
Numerical Aperture NA : 0.10
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
REACH 201 : Compliant
Certificate of Conformance : View