

TECHSPEC® 6.25mm Dia. x 35mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-309-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 + **A\$131.20**

ADD TO CART

Qty 1-5
A\$131.20
Qty 6+
A\$104.80
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.25 ±0.025

Effective Focal Length EFL (mm):
35.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 33.59
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 5.625
Centering (arcmin) : <1
Center Thickness CT (mm) : 3.20 ±0.10
Center Thickness CT 1 (mm) : 2.30 ±0.05
Center Thickness CT 2 (mm) : 0.90 ±0.05
Radius R₁ (mm) : 23.14
Radius R₂ (mm) : -14.51
Radius R₃ (mm) : -38.86
Edge Thickness ET (mm) : 2.86
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 5.6
Numerical Aperture NA : 0.09
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View