

TECHSPEC® 6.25mm Protected Silver Coated, N-BK7 Right Angle Mirror



Stock #89-625 3-5 DAYS

-

1

+

A\$140.00

ADD TO CART

Qty 1-5

A\$140.00

Qty 6+

A\$112.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Surface Flatness (P-V):
λ/8

Substrate:

N-BK7

Surface Quality:
20-10

Length of Legs (mm):

6.25
Dimensional Tolerance (mm): ±0.1
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 7.96 x 5.63
Length of Hypotenuse (mm): 8.80
Type: Right Angle Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
