

LightPath 354240 | 633nm Alignment, 0.50 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#67-727**

3-5 DAYS

-

1

+

A\$328.00

ADD TO CART

Qty 1-10

A\$328.00

Qty 11+

A\$289.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):  
8.00 @ 780nm

Numerical Aperture NA:  
0.50

|                                                                                                                               |
|-------------------------------------------------------------------------------------------------------------------------------|
| <b>Substrate:</b> <br><a href="#">ECO-550</a> |
| <b>Coating:</b><br>BBAR (600-1050nm)                                                                                          |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <1.0% @ 600 - 1050nm                                                        |
| <b>Surface Quality:</b><br>40-20                                                                                              |
| <b>Clear Aperture CA (mm):</b><br>8.00                                                                                        |
| <b>f#:</b><br>1.00                                                                                                            |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                   |
| <b>Connector:</b><br>SMA                                                                                                      |
| <b>Construction:</b><br>304L Stainless Steel Housing                                                                          |
| <b>Housing Diameter (mm):</b><br>12.00                                                                                        |
| <b>Housing Length (mm):</b><br>12.7                                                                                           |
| <b>Lightpath Lens Code:</b><br>354240                                                                                         |
| <b>Mount:</b><br>M12 x0.5                                                                                                     |
| <b>Type:</b><br>Fiber Collimator                                                                                              |
| <b>Wavelength Range (nm):</b><br>600 - 1050                                                                                   |
| <b>Conjugate Distance:</b><br>Infinite                                                                                        |
| <b>Lens Included:</b><br><a href="#">#37-103</a>                                                                              |
| <b>Alignment Wavelength (nm):</b><br>633                                                                                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |