

LightPath 354220 | 633nm Alignment, 0.25 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#67-725** 3-5 DAYS

- 1 + **A\$288.00**

ADD TO CART

Qty 1-10
A\$288.00
Qty 11+
A\$253.60
Volume Pricing
Request Quote

Get Product Downloads

Effective Focal Length EFL (mm):
11.00 @633nm

Numerical Aperture NA:
0.25

Substrate: D-ZK3
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.50
f#: 2.00
Bevel: Protective bevel as needed
Connector: SMA
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 17.1
Lightpath Lens Code: 354220
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Lens Included: #87-118
Alignment Wavelength (nm): 633

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant