

[See all 5 Products in Family](#)

## Everix Ultra-Thin OD 2 Shortpass Filter, 650nm, 12.5mm Square

See More by [Everix](#)



Ultra-Thin Shortpass Filters

Stock #35-895 CLEARANCE **13 In Stock**

⊖ 1 ⊕ **A\$118<sup>40</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-10	<b>A\$118.40</b> each
Qty 11+	<b>A\$106.56</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Flexible Filter **Type:**

#### Physical & Mechanical Properties

12.5 x 12.5 ±0.2 **Dimensions (mm):**

12.50 **Length (mm):**

Width (mm):

12.50

Clear Aperture (%):

>90

## Optical Properties

Optical Density OD (Average):

2.0 (average)

Cut-Off Wavelength (nm):

650.00

Transmission (%):

>80 (average)

Transmission Wavelength (nm):

400 - 620 (typical)

Blocking Wavelength Range (nm):

680 - 795 (typical)

Cut-Off Tolerance (%):

±3 (typical)

## Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

## Product Details

- Flexible Design to Conform to Curved Surfaces
- Scratch Insensitive, Ultra-thin Polymer Construction
- >80% Average Transmission

Everix Ultra-Thin Shortpass Filters are constructed from layers of ultra-thin polymers and dyes that deliver the same performance as thick traditional filters but in a compact, flexible filter design. The all-plastic composition of these flexible shortpass filters makes them both shatter proof and insensitive to scratching. Less than 500 microns thick, these flexible filters provide high transmission and a blocking optical density (OD) of 2.0 outside of transmission range. Everix Ultra-Thin Shortpass Filters are available with sharp cut-off wavelengths across the visible and near-infrared (NIR) spectra. These filters are an excellent solution for vision or medical applications requiring low cost, space saving optical filters.

**Note:** Custom filter designs can be purchased directly from [Everix](#).

## Technical Information

