

## 656.3nm CWL, 12.5mm Dia., High Transmission Traditional Coated 10nm Bandpass Filter



High Transmission Traditional Coated Bandpass Filters

Stock **#71-682** **1 In Stock**

-

1

+

A\$184<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | A\$184.00 each                |
| Qty 11-25      | A\$156.40 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

### SPECIFICATIONS

#### General

Type:

Bandpass Filter

#### Physical & Mechanical Properties

Diameter (mm):

|                                       |                                          |
|---------------------------------------|------------------------------------------|
| 12.50 +0/-0.25                        |                                          |
| 9.0                                   | Clear Aperture CA (mm):                  |
| 5.90                                  | Thickness (mm):                          |
| Mounted in Black Anodized Ring        | Construction:                            |
| Optical Properties                    |                                          |
| 656.30                                | Center Wavelength CWL (nm):              |
| +2/-0                                 | Center Wavelength CWL Tolerance (nm):    |
| 10.00                                 | Full Width-Half Max FWHM (nm):           |
| ±2                                    | Full Width-Half Max FWHM Tolerance (nm): |
| 80                                    | Minimum Transmission (%):                |
| Traditional Coated                    | Coating:                                 |
| 1x10 <sup>-4</sup> avg Xray to 1000nm | Blocking Wavelength Range (nm):          |
| Environmental & Durability Factors    |                                          |
| -50 to +70                            | Operating Temperature (°C):              |
| Regulatory Compliance                 |                                          |
| Compliant                             | RoHS 2015:                               |
| View                                  | Certificate of Conformance:              |
| Compliant                             | REACH 241:                               |

## PRODUCT DETAILS

- Passband Transmission up to 80%
- 441.6 to 1064nm Wavelength Options with 10, 20, and 40nm Bandwidths
- Ideal for Medical and Analytical Applications

High Transmission Traditional Coated Bandpass Filters are designed for situations where far-infrared blocking is not required, allowing for up to 80% transmission in the passband region and good blocking over the visible and NIR wavelength range. Featuring popular laser, mercury, biomedical, and analytical spectral lines, these filters cover a wide range of visible and NIR wavelengths. A hermetic seal and an anodized metal mount help maintain performance in high humidity environments and protect against chipping and scratching. High Transmission Traditional Coated Bandpass Filters are ideal for a range of scientific and medical applications such as spectral radiometry, medical diagnostics, chemical analysis, and Colorimetry. For applications requiring wider blocking ranges, [traditional coated bandpass filters](#) are available whereas applications requiring higher transmission above 90% are best served with [hard coated bandpass filters](#).