

TECHSPEC® 6mm Dia. x 24mm FL, MgF₂ Coated, Double-Convex Lens



Stock **#32-868** 3-5 DAYS

[Other Coating Options](#)



1



A\$55.20

ADD TO CART

Qty 1-9

A\$55.20

Qty 10+

A\$49.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
6.00 +0.0/-0.025

Back Focal Length BFL (mm):
23.13

Effective Focal Length EFL (mm): 24.00
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 2.60
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 2.23
Radius R₁=R₂ (mm): 24.36
Clear Aperture CA (mm): 5.4
f/#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View