


TECHSPEC® 6mm Dia. x -9mm FL, NIR II, Inked, Double-Concave Lens



Stock **#68-006-INK** 10-15 DAYS
[Other Coating Options](#)

- 1 + **A\$77.60**

ADD TO CART

Qty 1-9
A\$77.60
Qty 10+
A\$70.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.00 ±0.025

Effective Focal Length EFL (mm):
-9.00

Substrate: N-BK7
f/#: 1.5
Numerical Aperture NA: 0.33
Coating: NIR II (750-1550nm)
Type: Double-Concave Lens
Wavelength Range (nm): 750 - 1550
Back Focal Length BFL (mm): -9.32
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <3
Clear Aperture CA (mm): 5.40
Coating Specification: R_{abs} ≤1.5% @ 750 - 800nm R_{abs} ≤1.0% @ 800 - 1550nm R_{avg} ≤0.7% @ 750 - 1550nm
Edge Thickness ET (mm): 1.79
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Radius R₁=R₂ (mm): -9.47
Surface Quality: 40-20
Damage Threshold, By Design: 8 J/cm² @ 1064nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View