

700µm Aperture Diameter, Chrome on Glass Aperture



Stock **#90-746** NEW **1 In Stock**

-

1

+

A\$296^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$296.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

Outer Diameter (mm):

25.4

Fixed Aperture Diameter (µm):

700 ± 5.0

Thickness (inches):

0.06 ±0.004

±0.1	Thickness Tolerance (mm):
1.52	Thickness (mm):
Optical Properties	
Low Reflective Chrome	Coating:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Chrome Coating on Glass Substrate
- Ideal for Precise Beam Control, Modulation, or Optical Alignment
- Pinhole Diameters Ranging from 10µm to 1,000µm

Chrome Coated Glass Optical Apertures are composed of soda lime float glass with low reflective chrome coating for high-contrast performance. These apertures are designed with pinhole diameters ranging from 10µm to 1000µm. The apertures have an overall diameter of 25.4mm (1") and a thickness of 1.52mm, ensuring easy integration with a wide variety of optical mounts. Chrome coating on glass provides a stable and circular aperture diameter immune to bending or creasing. Chrome Coated Glass Optical Apertures are designed to provide high-precision light control, ideal for beam shaping, spatial filtering, and alignment in advanced photonic systems.