

TECHSPEC® 700nm 25mm Diameter, OD 4.0 Shortpass Filter



High Performance OD 4.0 Shortpass Filters

Stock **#84-714** 3-5 DAYS

- 1 + **A\$409.60**

ADD TO CART

Qty 1-5

A\$409.60

Qty 6+

A\$328.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Cut-Off Wavelength (nm): 700.00
Substrate:  Fused Silica (Coming 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 715 - 1050
Surface Quality: 60-40
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.1
Transmission (%): ≥91
Transmission Wavelength (nm): 400 - 685
Type: Shortpass Filter
Clear Aperture (%): >80
Transmitted Wavefront, RMS: ≤λ/4 @ 633nm (prior to coating)
Slope Factor (%): <1
Cut-Off Tolerance (%): ±1
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Note: Arrow on part indicates filter coated surface.
Wavelength Range (nm): 400 - 1050

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant