

[See all 35 Products in Family](#)

75µm Aperture Diameter, 12.7mm Mounted, Acktar Blackened Pinhole

See More by [Acktar](#)



Acktar Blackened Pinholes (mounted)



Stock **#16-823** [CONTACT US](#)

-

1

+

A\$308⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$308.80 each
Qty 10+	A\$277.92 each
Need More?	Request Quote

Product Downloads

General	
Mounted	Type:
PA-1-2-75-05	Model Number:
Physical & Mechanical Properties	

12.7 ±0.2	Outer Diameter (mm):
Stainless Steel	Construction:
75 ±3	Fixed Aperture Diameter (µm):
20 nominal	Thickness (µm):

Optical Properties

Magic Black™	Coating:
--------------	----------

Threading & Mounting

12.7 ±0.2	Diameter of Mount (mm):
2.0 ±0.1	Mount Thickness (mm):

Material Properties

99	Absorbance (%):
----	-----------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Low Reflectance from the EUV to SWIR
- 99% Absorbance Blackening Coating
- Aperture Sizes from 20 to 1000µm
- Available Unmounted and Mounted

Acktar Blackened Pinholes feature Acktar Magic Black™ blackening coating that provides wide-band low reflectance from the extreme ultraviolet (EUV) to the short-wave infrared (SWIR). This coating provides near zero outgassing and can be used in temperatures up to 380°C. Acktar Blackened Pinholes are coated on both sides, including the pinhole edge, and are available either unmounted or mounted in a 25mm mount for easy integration into optical systems. These stainless steel substrate pinholes are ideal for spatial filtering applications requiring low back reflection and scattering from light sources.

Note: Please [contact us](#) for custom aperture options.