

TECHSPEC® 75 x 75mm Wire Grid Polarizing Film



TECHSPEC® Wire Grid Polarizing Film

Stock **#33-084** CLEARANCE 3-5 DAYS

-

1

+

A\$268.72

ADD TO CART

Qty 1+

A\$268.72

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0 - 45

Extinction Ratio:
>4,250:1 @550nm

Substrate: ☐
[Aluminum Wires on TAC Film](#)

Length (mm):
75.00

Operating Temperature (°C): 60 Max @ 90% RH 105 in dry conditions
Dimensions (mm): 75.0 x 75.0
Thickness (mm): 0.08
Transmission (%): 85 (for p-polarized light @ 550nm)
Type: Linear Polarizer
Dimensional Tolerance (mm): +0/-0.5
Construction: Wire Grid
Wavelength Range (nm): 400 - 1200
Width (mm): 75.00
Axis Orientation: 0° ± 1.5°, marked by Notch

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Contains SVHC(s)